



ERT

Multi-Channel RTD Response Time Test Unit



About

A PC-based system including hardware, software, training, and documentation is offered by AMS for in-situ response time testing of RTDs using the Loop Current Step Response (LCSR) technique. With this system, up to 5 RTDs can be tested simultaneously to reduce test time and to increase the efficiency of the measurements. This system incorporates over 30 years of AMS experience in RTD response time testing in nuclear power plants. The AMS system is designed to sample and analyze the LCSR data, to obtain the response times of RTDs, to display the results on a computer screen, to print the results, and to store the data for trending.

LCSR Analyzer / Calibration Unit

Laptop Computer with USB Communication to ERT Signal Generator & MLCSR Software Provides User Interface for:

- Configuration of Sensors
- Configuration of Data Acquisition Parameter
- Display of LCSR Data as it's Being Acquired
- Averaging of Multiple Data Sets to Minimize the Effects of Temperature Streaming
- Analysis of Data and Display of Results
- Recording of Plant Conditioning During Tests
- Saving Data
- Viewing Previously Saved Data

Calibration Unit - ELC-Q:

Used to provide a functional test of ERT and LCSR Analyzer prior to in-plant tests

Dimensions: 8" x 6" x 11"

Weight: 6 lbs (2.7 kg)

Power Requirements: 110 - 255 VAC 47-63 Hz, 10 Watts

Temperature/Humidity: 0 - 45°C / 5 - 95% non-condensing

Model ERT LCSR Signal Generator

Resistance Range: 50 - 500 \pm 2.5% FS

Bridge Output Range: +/- 10 Volts

Anti-alias Low Pass Filter: 495 Hz

Power Supplied to RTD: Variable between 0.01-9 watts

Number of Channels: One to Five, Selectable

Input Connection: 4 mm Banana Jacks

Signal Gain: 20 - 1000

CMR (\emptyset -6 \emptyset Hz): 11 \emptyset db

RTD Current Accuracy: +/- 2.0%

Dynamic Resolution: 16 bits, 1 in 65, 536

Sampling Interval: 0.01 to 0.10 Seconds

Warm-up Time: 15 Minutes Recommended

Power Requirements: 110 - 255 VAC 47-63 Hz, 80 Watts

Dimensions: 14" x 14" x 8"

Weight: 9 lbs (8.6 kg)

Temperature/Humidity: 0 - 45°C / 5 - 95% non condensing

For more information please contact:

Dan Beverly (Chief Technical Officer)
Extension: 112 **Email:** dan@ams-corp.com

Darrell W. Mitchell (Technical Services Manager)
Extension: 108 **Email:** darrell@ams-corp.com

Analysis and Measurement Services Corporation

AMS Technology Center
9119 Cross Park Drive
Knoxville, TN 37923, USA

TEL 865 691 1756
FAX 865 691 9344

EMAIL info@ams-corp.com
WEB www.ams-corp.com

*** 10CFR50 Appendix B Program**